

2STFSD747512SS Cut Sheet



Hammond disconnect enclosure, slope top, NEMA 3R/4/4X/12/13, right flange, 79 x 75 x 13in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, double-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2STFSD747512SS>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	Yes
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	79 x 75 x 13in (HxWxD)
Enclosure Height	78.54in
Enclosure Width	75.13in
Enclosure Depth	13.38in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No

Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point 316 stainless steel padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2STFSD747512SS.pdf>
See store item page for other formats.