

2STFSD747524SS Cut Sheet



Hammond disconnect enclosure, slope top, NEMA 3R/4/4X/12/13, right flange, 83 x 75 x 25in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, double-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2STFSD747524SS>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	Yes
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	83 x 75 x 25in (HxWxD)
Enclosure Height	82.91in
Enclosure Width	75.13in
Enclosure Depth	25.38in

Mounting	Freestanding
Integral Mounting Feet	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point 316 stainless steel padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2STFSD747524SS.pdf>
See store item page for other formats.