

2UD726218FFTC Cut Sheet



Hammond disconnect enclosure, NEMA 12, right flange, 72 x 62 x 18in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2UD726218FFTC>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12
IP Rating	IP54
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 62 x 18in (HxWxD)
Enclosure Height	72.13in
Enclosure Width	62.00in
Enclosure Depth	19.35in
Mounting	Floor

Integral Mounting Feet	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2UD726218FFTC.pdf>
See store item page for other formats.