

# 2UDCP606112FFTC Cut Sheet



Hammond disconnect enclosure, NEMA 12, center post, 60 x 61 x 12in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2UDCP606112FFTC>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>NEMA Rating</b>	12
<b>IP Rating</b>	IP54
<b>Disconnect Mounting</b>	Center post
<b>Nominal Enclosure Dimensions</b>	60 x 61 x 12in (HxWxD)
<b>Enclosure Height</b>	60.13in
<b>Enclosure Width</b>	60.88in
<b>Enclosure Depth</b>	13.35in
<b>Mounting</b>	Floor
<b>Dual Access</b>	No
<b>Knockouts</b>	No

<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	Lift-off hinges
<b>Number of Hinges Per Door</b>	3
<b>Latch Type</b>	3-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Subpanel included
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR21001
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2UDCP606112FFTC.pdf>  
See store item page for other formats.