

2UDCP727318FFTC Cut Sheet



Hammond disconnect enclosure, NEMA 12, center post, 72 x 73 x 18in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2UDCP727318FFTC>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Hammond |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 12 |
| IP Rating | IP54 |
| Disconnect Mounting | Center post |
| Nominal Enclosure Dimensions | 72 x 73 x 18in (HxWxD) |
| Enclosure Height | 72.13in |
| Enclosure Width | 72.88in |
| Enclosure Depth | 19.35in |
| Mounting | Floor |

| | |
|----------------------------------|---------------------------|
| Integral Mounting Feet | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | 2-door |
| Hinge Type | Lift-off hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Subpanel included |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2UDCP727318FFTC.pdf>
See store item page for other formats.