2UHD726718FTC Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Hammond disconnect enclosure, NEMA 12, right flange, 72 x 67 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/2UHD726718FTC

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12
IP Rating	IP54
Disconnect Mounting	Right flange
Nominal Enclosure Height	72in
Nominal Enclosure Width	67in
Nominal Enclosure Depth	18in
Mounting	Freestanding

Integral Mounting Feet	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2UHD726718FTC.pdf
See store item page for other formats.