

30002D Cut Sheet



Bryant manual motor controller, open, 30A, 600 VAC, 2-pole, 15hp, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/30002D>

Technical Specifications

| | |
|-------------------------------|------------------------------------|
| Brand | Bryant |
| Item | Manual motor controller |
| Body Type | Open |
| Amperage Rating | 30A |
| Voltage Rating | 600 VAC |
| Number of Poles | 2 |
| Horsepower Rating | 15hp |
| Wiring Type | Can be wired from the back or side |
| UL Rating | UL 508 rated |
| Additional Information | Suitable as motor disconnect |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E70402 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 46186 |
| RoHS Status | No |
| EU REACH | View EU REACH document |