

# 30102D Cut Sheet



Bryant manual motor controller, enclosed, 30A, 600 VAC, 2-pole, 15hp, wall mount, aluminum housing, NEMA 1, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/30102D>

## Technical Specifications

Brand	Bryant
Item	Manual motor controller
Body Type	Enclosed
Amperage Rating	30A
Voltage Rating	600 VAC
Number of Poles	2
Horsepower Rating	15hp
Mounting	Wall
Handle Type	Standard toggle
Housing Material	Aluminum
Housing Rating	NEMA 1
Wiring Type	1/2in and 3/4in NPT top, bottom, or back wiring conduit knockouts
Includes	NEMA 1 enclosure and 30002D standard toggle controller
Application	Ideal for use in indoor environments
UL Rating	UL 508 rated
Additional Information	Lockout/tagout capable. Suitable as motor disconnect

## Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	46186
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>