

# 30302D Cut Sheet



Bryant manual motor controller, enclosed, 30A, 600 VAC, 2-pole, 15hp, wall mount, die-cast aluminum housing, NEMA 3R, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/30302D>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Manual motor controller
<b>Body Type</b>	Enclosed
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	600 VAC
<b>Number of Poles</b>	2
<b>Horsepower Rating</b>	15hp
<b>Mounting</b>	Wall
<b>Handle Type</b>	Red external lever

<b>Housing Material</b>	Die-cast aluminum
<b>Housing Rating</b>	NEMA 3R
<b>Wiring Type</b>	(3) 1/2in NPT threaded openings on top, bottom, and back of enclosure
<b>Includes</b>	NEMA 3R enclosure and 30002D standard toggle controller
<b>Application</b>	Ideal for use in indoor and outdoor environments
<b>UL Rating</b>	UL 508 rated
<b>Additional Information</b>	Lockout/tagout capable. Suitable as motor disconnect

## Agency Approvals

<b>UL Listed File #</b>	E70402
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	46186
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/30302D.pdf>  
See store item page for other formats.