

30302D Cut Sheet



Bryant manual motor controller, enclosed, 30A, 600 VAC, 2-pole, 15hp, wall mount, die-cast aluminum housing, NEMA 3R, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/30302D>

Technical Specifications

Brand	Bryant
Item	Manual motor controller
Body Type	Enclosed
Amperage Rating	30A
Voltage Rating	600 VAC
Number of Poles	2
Horsepower Rating	15hp
Mounting	Wall
Handle Type	Red external lever
Housing Material	Die-cast aluminum
Housing Rating	NEMA 3R
Wiring Type	(3) 1/2in NPT threaded openings on top, bottom, and back of enclosure
Includes	NEMA 3R enclosure and 30002D standard toggle controller
Application	Ideal for use in indoor and outdoor environments
UL Rating	UL 508 rated
Additional Information	Lockout/tagout capable. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	46186
RoHS Status	No
EU REACH	View EU REACH document