

30323D Cut Sheet



Bryant manual motor controller, enclosed, 30A, 600 VAC, 3-pole, 20hp, wall mount, thermoplastic housing, NEMA 3R, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/30323D>

Technical Specifications

Brand	Bryant
Item	Manual motor controller
Body Type	Enclosed
Amperage Rating	30A
Voltage Rating	600 VAC
Number of Poles	3
Horsepower Rating	20hp
Mounting	Wall
Handle Type	Red external lever
Housing Material	Thermoplastic
Housing Rating	NEMA 3R
Wiring Type	Installer determined wire entry, no pre-drilled openings or knockouts
Includes	NEMA 3R enclosure and 30003DS standard toggle controller
Application	Ideal for use in indoor and outdoor environments
UL Rating	UL 508 rated
Additional Information	Lockout/tagout capable. Chemical and impact resistant. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	46186
RoHS Status	No
EU REACH	View EU REACH document