

3035303 Cut Sheet



Seifert SoliTherm thermoelectric cooler, 100 BTU/H, 24 VDC operating voltage, 304 stainless steel housing, filter-free, recessed mount. For use with NEMA 4/4X/12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3035303>

Technical Specifications

Brand	Seifert
Series	SoliTherm
Item	Thermoelectric cooler
Nominal Cooling Capacity	100 BTU/H
Operating Voltage	24 VDC
Running Current	1.4A
Height	6.04in
Width	4.33in

Depth	5.06in
Mounting	Recessed
Filter-Free	Yes
Housing Material	304 stainless steel
IP Rating	IP66
For Use With	NEMA 4/4X/12 enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	SA32278
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/3035303.pdf>
See store item page for other formats.