

# 3050303 Cut Sheet



Seifert SoliTherm thermoelectric cooler, 170 BTU/H, 24 VDC operating voltage, 304 stainless steel housing, filter-free, recessed mount. For use with NEMA 4/4X/12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3050303>

## Technical Specifications

<b>Brand</b>	Seifert
<b>Series</b>	SoliTherm
<b>Item</b>	Thermoelectric cooler
<b>Nominal Cooling Capacity</b>	170 BTU/H
<b>Operating Voltage</b>	24 VDC
<b>Running Current</b>	2.5A
<b>Height</b>	8.11in
<b>Width</b>	6.06in

<b>Depth</b>	5.31in
<b>Mounting</b>	Recessed
<b>Filter-Free</b>	Yes
<b>Housing Material</b>	304 stainless steel
<b>IP Rating</b>	IP66
<b>For Use With</b>	NEMA 4/4X/12 enclosures
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	SA32278
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/3050303.pdf>  
See store item page for other formats.