

3124270 Cut Sheet



Murrelektronik solenoid valve surge suppressor, resistor-capacitor, 48-130 VAC/VDC, 1-phase, 0-60Hz, 10W, vertical mount. For use with 11mm DIN style Form B plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3124270>

Technical Specifications

Brand	Murrelektronik
Application	Solenoid valve
Item	Surge suppressor
Circuit Type	Resistor-capacitor
Voltage Rating	48-130 VAC/VDC
Number of Phases	1
Frequency	0-60Hz
Power Rating	10W
Indicating Type	LED indication
Mounting	Vertical
For Use With	11mm DIN style Form B plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/3124270.pdf>
See store item page for other formats.