

3400-2010 Cut Sheet



Trumeter electrical counter, 7mm 8-digit LCD, 10-300 VDC or 20-300 VAC input, remote reset, rectangular flush mount with clip, 1/4in (6.4mm) spade terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3400-2010>

Technical Specifications

Brand	Trumeter
Item	Counter
Counter Type	Electrical
Count Direction	Up
Count Speed	40Hz
Display Type	LCD
Display Size	7mm 8-digit
Reset	Remote
Input	10-300 VDC or 20-300 VAC
Mounting	Panel
Mounting Type	Rectangular flush mount with clip
Mounting Hole Size	1.46 x 0.94in
Connector Type	1/4in (6.4mm) spade terminals
Additional Information	NEMA 4/4X, 12 & IP66 compliant from the front when using the optional gasket
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Battery• Battery Type: Other• Generic Battery: CR2032

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document