

34671 Cut Sheet

Viking mechanic-length drill bit, 5/16in, split point, high-speed steel (HSS), black and gold oxide finish, 1/4in hex shank, 4in (102mm) overall length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/34671>

Technical Specifications

Brand	Viking	Point Angle	135 degrees
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	1/4in hex
Drill Bit Type	Mechanic-length	Overall Length	4in (102mm)
Size	5/16in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Material	High-speed steel (HSS)	Application	Hole cutting
Finish	Black and gold oxide	Quantity per Pack	2
Flute Length	2-1/2in		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement