

# 34811 Cut Sheet



Viking mechanic-length drill bit set, 12 pieces, high-speed steel (HSS), 1/4in hex shank, imperial, gold oxide finish, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/34811>

## Technical Specifications

Brand	Viking	Shank Type	1/4in hex
Item	Drill bit set	Application	Hole cutting
Number of Pieces	12	For Use On	Stainless steel, iron and steel
Material	High-speed steel (HSS)	Measurement Type	Imperial
Drill Bit Type	Mechanic-length	Package Type	Plastic case
Drill Bit Size	1/16in, 3/32in, 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in	Set Includes	Includes (12) 1/4in hex drill bits (1/16in, 3/32in, 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in), (1) quick release adaptor, plastic carrying case
Finish	Gold oxide		
Point Angle	135 degrees		
Point Cut	Split		

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>