

# 3516-6Q001-BAC7B-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., low lead brass body, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), Cv=4.5, 180 psi maximum operating pressure, 120 VAC operating voltage, 18in 22 AWG pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3516-6Q001-BAC7B-A>

## Technical Specifications

<b>Brand</b>	Spartan
<b>Series</b>	3516
<b>Item</b>	Valve
<b>Working Fluid</b>	Potable water
<b>Valve Type</b>	Solenoid process
<b>Port Quantity</b>	2-way
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Operator Type</b>	Diaphragm
<b>Action</b>	Single solenoid spring return
<b>Body Material</b>	Low lead brass
<b>IP Rating</b>	IP65
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Flow Coefficient</b>	4.5
<b>Maximum Operating Pressure</b>	180 psi
<b>Minimum Operating Pressure</b>	10 psi
<b>Operating Voltage</b>	120 VAC
<b>Electrical Connection</b>	18in 22 AWG pigtail

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>