

3541RAC Cut Sheet



RACO connector, liquid-tight, 90-degree, 3/8in trade size, 1/2in NPT thread type, insulation, zinc electro-plated finish. Package of 25. For use with Liqueatite electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3541RAC>

Technical Specifications

Brand	RACO
Item	Connector
Liquid-tight	Yes
Connector Type	90-degree
Material	Steel
Trade Size	3/8in
Thread Type	1/2in NPT
Insulation	Yes
Finish	Zinc electro-plated
Quantity per Pack	25
For Use With	Liquatite electrical conduit
Includes	Sealing washer and locknut

Agency Approvals

UL Listed File #	E195969
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	1456072
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3541RAC.pdf>
See store item page for other formats.