3580-060-8213C-A Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Spartan solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, FKM seal(s), 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=1.55, 7 psi minimum operating pressure, 24 VDC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/3580-060-8213C-A

Technical Specifications

Brand	Spartan
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Series	3580
IP Rating	IP65
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return

Body Material	Glass-filled nylon
Seal Material	FKM
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	1.55
Maximum Operating Pressure	150 psi
Minimum Operating Pressure	7 psi
Working Fluid Temperature	60–140 °F
Operating Voltage	24 VDC
Electrical Connection	11mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/3580-060-8213C-A.pdf
See store item page for other formats.