

3580-060-8237C-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), Cv=2.45, 150 psi maximum operating pressure, 120 VAC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3580-060-8237C-A>

Technical Specifications

Brand	Spartan
Series	3580
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Diaphragm
Action	Single solenoid spring return
Body Material	Glass-filled nylon
IP Rating	IP65
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Flow Coefficient	2.45
Maximum Operating Pressure	150 psi
Minimum Operating Pressure	7 psi
Operating Voltage	120 VAC
Electrical Connection	11mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document