

3825-66-B20Y-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., acetal body, 1/4in push-to-connect tubing inlet(s), 1/4in push-to-connect tubing outlet(s), Cv=0.24, 150 psi maximum operating pressure, 120 VAC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3825-66-B20Y-A>

Technical Specifications

Brand	Spartan
Series	3825
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Direct acting
Action	Single solenoid spring return
Body Material	Acetal

IP Rating	IP65
Inlet Port	1/4in push-to-connect tubing
Outlet Port	1/4in push-to-connect tubing
Flow Coefficient	0.24
Maximum Operating Pressure	150 psi
Minimum Operating Pressure	Vacuum
Operating Voltage	120 VAC
Electrical Connection	11mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/3825-66-B20Y-A.pdf>
See store item page for other formats.