

38503060 Cut Sheet



Socomec FUSERBLOC series rotary disconnect switch, fusible, Class J, load break capable, 3-pole, 600 VAC/250 VDC, 600A, 200kA SCCR, panel mount, UL 98 rated, front or side operated, accepts 12 x 12mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38503060>

Technical Specifications

Brand	Socomec
Item	Disconnect switch
Series	FUSERBLOC
Fuse Class	Class J
Fusible	Yes
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VAC/250 VDC
Amperage Rating	600A
SCCR Rating	200kA SCCR
Mounting	Panel
UL Rating	UL 98 rated
Configuration	Front or side operated
Shaft Size	Accepts 12 x 12mm size shaft
Handle Type	Rotary
Additional Information	Line terminal shrouds included. Purchase fuses and handle separately. Load terminal shrouds and lugs sold separately

Agency Approvals

UL Listed File #	E201138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	112964
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document