


# 38613005 Cut Sheet



Socomec FUSERBLOC series rotary disconnect switch, fusible, Class J, load break capable, 3-pole, 600 VAC/250 VDC, 60A, 100kA SCCR, DIN rail or panel mount, UL 98 rated, front or side operated, accepts 10 x 10mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38613005>

## Technical Specifications

<b>Brand</b>	Socomec
<b>Item</b>	Disconnect switch
<b>Series</b>	FUSERBLOC
<b>Fuse Class</b>	Class J
<b>Fusible</b>	Yes
<b>Load Break Capable</b>	Yes
<b>Number of Poles</b>	3
<b>Voltage Rating</b>	600 VAC/250 VDC
<b>Amperage Rating</b>	60A
<b>SCCR Rating</b>	100kA SCCR
<b>Mounting</b>	DIN rail or panel
<b>UL Rating</b>	UL 98 rated
<b>Configuration</b>	Front or side operated
<b>Shaft Size</b>	Accepts 10 x 10mm size shaft
<b>Handle Type</b>	Rotary
<b>Additional Information</b>	Purchase fuses and handle separately

## Agency Approvals

<b>UL Listed File #</b>	E201138
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	112964
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>