

# 3ACTR030-42-24-F Cut Sheet



AcuAMP AC current transducer, 3-phase, fixed core, 0-10, 0-15, or 0-30A selectable sensing range, True RMS, 4-20 mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3ACTR030-42-24-F>

## Technical Specifications

|                       |                                 |
|-----------------------|---------------------------------|
| Brand                 | AcuAMP                          |
| Item                  | Current transducer              |
| Voltage Type          | AC                              |
| Number of Phases      | 3                               |
| Body Type             | Fixed core                      |
| Sensing Range         | 0-10, 0-15, or 0-30A selectable |
| True RMS              | Yes                             |
| Output                | 4-20 mA                         |
| Operating Voltage     | 24 VAC/VDC                      |
| Mounting              | Panel or 35mm DIN rail          |
| Electrical Connection | Screw terminals                 |
| UL Rating             | UL 508 listed                   |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E197592                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/3ACTR030-42-24-F.pdf>  
See store item page for other formats.