

3ACTR100-42-24-F Cut Sheet



AcuAMP AC current transducer, 3-phase, fixed core, 0-30, 0-50, or 0-100A selectable sensing range, True RMS, 4-20 mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3ACTR100-42-24-F>

Technical Specifications

| | |
|------------------------------|----------------------------------|
| Brand | AcuAMP |
| Item | Current transducer |
| Voltage Type | AC |
| Number of Phases | 3 |
| Body Type | Fixed core |
| Sensing Range | 0-30, 0-50, or 0-100A selectable |
| True RMS | Yes |
| Output | 4-20 mA |
| Operating Voltage | 24 VAC/VDC |
| Mounting | Panel or 35mm DIN rail |
| Electrical Connection | Screw terminals |
| UL Rating | UL 508 listed |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E197592 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3ACTR100-42-24-F.pdf>
See store item page for other formats.