


# 3NK4HP Cut Sheet



Fuji Electric 3NK4 series thermal overload relay, 125.0-185.0A adjustable, bi-metallic, direct mount power connection(s), panel mount. For use with 3NC4Hx contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3NK4HP>

## Technical Specifications

<b>Brand</b>	Fuji Electric
<b>Item</b>	Relay
<b>Series</b>	3NK4
<b>Relay Type</b>	Thermal overload
<b>Full Load Amperage Range</b>	125.0-185.0A adjustable
<b>Operation Type</b>	Bi-metallic
<b>Auxiliary Contacts</b>	(1) N.O./ (1) N.C.
<b>Trip Class</b>	Trip Class 20
<b>Phase Loss Sensitive</b>	Yes
<b>Connection</b>	Direct mount power
<b>Mounting</b>	Panel
<b>For Use With</b>	3NC4Hx contactors

## Agency Approvals

<b>UL Listed File #</b>	E42419
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>