

# 3PU06MC20 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, black, clear blue and blue, triple 6mm outside diameter, 5/32in (4mm) inside diameter, 20 coils, 6.2ft (1.90m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3PU06MC20>

## Technical Specifications

|                              |                              |
|------------------------------|------------------------------|
| <b>Brand</b>                 | NITRA                        |
| <b>Item</b>                  | Pneumatic Coiled tubing      |
| <b>Material</b>              | Ether-based polyurethane     |
| <b>Color</b>                 | Black, clear blue and blue   |
| <b>Outside Diameter</b>      | Triple 6mm                   |
| <b>Inside Diameter</b>       | 5/32in (4mm)                 |
| <b>Number of Coils</b>       | 20                           |
| <b>Working Length</b>        | 6.2ft (1.90m) working length |
| <b>Operating Pressure</b>    | 180 psi                      |
| <b>Operating Temperature</b> | -40 to +160 deg F            |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |