

# 3PU38C20 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black, clear blue and blue, triple 3/8in outside diameter, 0.250in inside diameter, 20 coils, 8.3ft (2.53m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3PU38C20>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Bonded coiled tubing
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Ether-based polyurethane
<b>Color</b>	Black, clear blue and blue
<b>Outside Diameter</b>	Triple 3/8in
<b>Inside Diameter</b>	0.250in
<b>Number of Coils</b>	20
<b>Working Length</b>	8.3ft (2.53m) working length
<b>Operating Pressure</b>	150 psi
<b>Operating Temperature</b>	-40 to +160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>