

3PU38C40 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black, clear blue and blue, triple 3/8in outside diameter, 0.250in inside diameter, 40 coils, 16.0ft (4.88m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3PU38C40>

Technical Specifications

Brand	NITRA
Item	Bonded coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Black, clear blue and blue
Outside Diameter	Triple 3/8in
Inside Diameter	0.250in
Number of Coils	40
Working Length	16.0ft (4.88m) working length
Operating Pressure	150 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document