


3PU532-50 Cut Sheet



NITRA pneumatic bonded tubing, ether-based polyurethane, black, clear blue and blue, triple 5/32in outside diameter, 0.093in inside diameter, 50ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3PU532-50>

Technical Specifications

Brand	NITRA
Item	Bonded tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Black, clear blue and blue
Outside Diameter	Triple 5/32in
Inside Diameter	0.093in
Working Length	50ft package
Operating Pressure	200 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document