

3PU532C20 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black, clear blue and blue, triple 5/32in outside diameter, 0.093in inside diameter, 20 coils, 4.4ft (1.34m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3PU532C20>

Technical Specifications

Brand	NITRA
Item	Pneumatic Bonded coiled tubing
Material	Ether-based polyurethane
Color	Black, clear blue and blue
Outside Diameter	Triple 5/32in
Inside Diameter	0.093in
Number of Coils	20
Working Length	4.4ft (1.34m) working length
Operating Pressure	200 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document