

3UHD9011924N4SS Cut Sheet



Hammond disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 90 x 119 x 24in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 3-door, 3-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3UHD9011924N4SS>

Technical Specifications

Brand	Hammond	Mounting	Freestanding
Item	Disconnect enclosure	Integral Mounting Feet	No
Slope Top	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	3-door
IP Rating	IP66	Hinge Type	Lift-off hinges
Disconnect Mounting	Right flange	Number of Hinges Per Door	3
Nominal Enclosure Dimensions	90 x 119 x 24in (HxWxD)	Latch Type	3-point padlocking handle
Enclosure Height	90.13in	Padlockable	Yes
Enclosure Width	118.25in	Keylocking	No
Enclosure Depth	25.35in	Subpanel	(2) subpanels included

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3UHD9011924N4SS.pdf>
See store item page for other formats.