

3/8MXT-120IN-FJXEE Cut Sheet



Gates MXT petroleum based hydraulic fluid hose assembly, synthetic rubber, braided steel wire reinforced, black, 3/8in inside diameter, 0.675in outside diameter, (2) -6 female straight JIC 37 deg fittings, 10ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3/8MXT-120IN-FJXEE>

Technical Specifications

Brand	Gates
Item	Hose assembly
Series	MXT
Working Fluid	Petroleum based hydraulic fluid
Material	Synthetic rubber
Reinforcement	Braided steel wire
Color	Black
Inside Diameter	3/8in

Outside Diameter	0.675in
Connection	(2) -6 female straight JIC 37 deg fittings
Minimum Bend Radius	2.5in
Working Length	10ft working length
Operating Pressure	4800 psi
Operating Temperature	-40 to +212 deg F
Duty Rating	600,000 cycles

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document