

3/8PFX-48IN-FJXEE Cut Sheet



Gates ProFlex petroleum based hydraulic fluid hose assembly, synthetic rubber, braided steel wire reinforced, black, 3/8in inside diameter, 0.65in outside diameter, (2) -6 female straight JIC 37 deg fittings, 4ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3/8PFX-48IN-FJXEE>

Technical Specifications

| | | | |
|-----------------|---------------------------------|-----------------------|--|
| Brand | Gates | Outside Diameter | 0.65in |
| Item | Hose assembly | Connection | (2) -6 female straight JIC 37 deg fittings |
| Series | ProFlex | Minimum Bend Radius | 2.5in |
| Working Fluid | Petroleum based hydraulic fluid | Working Length | 4ft working length |
| Material | Synthetic rubber | Operating Pressure | 4800 psi |
| Reinforcement | Braided steel wire | Operating Temperature | -40 to +212 deg F |
| Color | Black | Duty Rating | 200,000 cycles |
| Inside Diameter | 3/8in | | |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |