

4000000020 Cut Sheet



Seifert fan hood, fits 3.62 x 3.62in fan cutout, 304 stainless steel, sanitary gasket, NEMA 3RX/4X/12K/13, IP56, for increasing the protection classification of side-mounted fans and grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4000000020>

Technical Specifications

Brand	Seifert
Item	Fan hood
Maximum Fan Cutout Size	3.62 x 3.62in
Maximum Covered Area	4.19 x 4.19in
Material	304 stainless steel
Gasket Type	Sanitary
NEMA Rating	3RX/4X/12K/13
IP Rating	IP56
Application	For increasing the protection classification of side-mounted fans and grilles

Agency Approvals

UL Listed File #	None
UL Recognized File #	E498756
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document