

# 4000100020 Cut Sheet



Seifert fan hood, fits 4.92 x 4.92in fan cutout, 304 stainless steel, sanitary gasket, NEMA 3RX/4X/12K/13, IP56, for increasing the protection classification of side-mounted fans and grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4000100020>

## Technical Specifications

Brand	Seifert
Item	Fan hood
Maximum Fan Cutout Size	4.92 x 4.92in
Maximum Covered Area	5.91 x 5.91in
Material	304 stainless steel
Gasket Type	Sanitary
NEMA Rating	3RX/4X/12K/13
IP Rating	IP56
Application	For increasing the protection classification of side-mounted fans and grilles

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E498756
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/4000100020.pdf>  
See store item page for other formats.