

# 41503026 Cut Sheet



Socomec SIRCOVER series rotary manual transfer switch, 3-pole, 600 VAC, 260A, 65kA SCCR, panel mount, UL1008 rated, front operated, accepts 15 x 12mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/41503026>

## Technical Specifications

<b>Brand</b>	Socomec
<b>Item</b>	Manual transfer switch
<b>Series</b>	SIRCOVER
<b>Fusible</b>	No
<b>Load Break Capable</b>	No
<b>Number of Poles</b>	3
<b>Voltage Rating</b>	600 VAC
<b>Amperage Rating</b>	260A
<b>SCCR Rating</b>	65kA SCCR
<b>Mounting</b>	Panel
<b>UL Rating</b>	UL1008 rated
<b>Configuration</b>	Front operated
<b>Shaft Size</b>	Accepts 15 x 12mm size shaft
<b>Handle Type</b>	Rotary
<b>Additional Information</b>	Purchase handle separately. Line & load terminal screens, lugs, and bridging bars sold separately

## Agency Approvals

<b>UL Listed File #</b>	E317092
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>