

41504026 Cut Sheet



Socomec SIRCOVER series rotary manual transfer switch, 4-pole, 600 VAC, 260A, 65kA SCCR, panel mount, UL1008 rated, front operated, accepts 15 x 12mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/41504026>

Technical Specifications

Brand	Socomec
Item	Manual transfer switch
Series	SIRCOVER
Fusible	No
Load Break Capable	No
Number of Poles	4
Voltage Rating	600 VAC
Amperage Rating	260A
SCCR Rating	65kA SCCR
Mounting	Panel
UL Rating	UL1008 rated
Configuration	Front operated
Shaft Size	Accepts 15 x 12mm size shaft
Handle Type	Rotary
Additional Information	Purchase handle separately. Line & load terminal screens, lugs, and bridging bars sold separately

Agency Approvals

UL Listed File #	E317092
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document