

# 44180 Cut Sheet



Viking jobber-length drill bit set, 13 pieces, high-speed steel (HSS), round shank, metric, black oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/44180>

## Technical Specifications

Brand	Viking	Point Cut	Split
Item	Drill bit set	Shank Type	Round
Number of Pieces	13	Application	Hole cutting
Material	High-speed steel (HSS)	For Use On	Stainless steel, iron and steel
Drill Bit Type	Jobber-length	Measurement Type	Metric
Drill Bit Size	1.0mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.0mm, 5.5mm, 6.0mm, 6.5mm and 7.0mm	Package Type	Metal index case
Finish	Black oxide	Set Includes	Includes (13) jobber-length drill bits (1.0mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.0mm, 5.5mm, 6.0mm, 6.5mm, 7.0mm), durable metal case
Point Angle	135 degrees		

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>