

45030055 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 1m, 2.8 kHz tone frequency, continuous tone(s), touch to acknowledge, 24 VDC, permanent LED indicator(s), yellow, 22mm, panel mount, polycarbonate housing, yellow, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/45030055>

Technical Specifications

Brand	WERMA
Item	Audible alarm buzzer
Loudness Decibel	80 dB at 1m
Tone Frequency	2.8 kHz
Tone Type	Continuous
Touch to Acknowledge	Yes
Voltage Rating	24 VDC
Indicator	Permanent LED
Light Color(s)	Yellow
Barrel Size	22mm
Mounting	Panel
Housing Material	Polycarbonate
Color	Yellow
IP Rating	IP65

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document