

46012074 Cut Sheet



WERMA EvoSIGNAL Mini TwinFLASH series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), red, 62mm, 12 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46012074>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Mini TwinFLASH
Bulb Type	LED
Operator Size	62mm
Operator Color	Red
Light Color(s)	Red
Light Function	Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing)
Housing Material	Polycarbonate

Material	ABS/polycarbonate
Loudness Decibel	95 dB at 1m
Tone Frequency	4 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Voltage Rating	12 VAC/VDC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/46012074.pdf>
See store item page for other formats.