

46031074 Cut Sheet



WERMA EvoSIGNAL Mini TwinLIGHT series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), permanent or blinking (1 Hz ON for 410ms), yellow, 62mm, 12 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46031074>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Mini TwinLIGHT
Bulb Type	LED
Operator Size	62mm
Operator Color	Yellow
Light Color(s)	Yellow
Light Function	Permanent or blinking (1 Hz ON for 410ms)
Housing Material	Polycarbonate
Material	ABS/polycarbonate
Loudness Decibel	95 dB at 1m
Tone Frequency	4 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Voltage Rating	12 VAC/VDC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document