

46031075 Cut Sheet



WERMA EvoSIGNAL Mini TwinLIGHT series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), permanent or blinking (1 Hz ON for 470ms), yellow, 62mm, 24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46031075>

Technical Specifications

| | | | |
|-------------------------|---|-----------------------------|------------------|
| Brand | WERMA | Loudness Decibel | 95 dB at 1m |
| Item | Audible-visual signal beacon | Tone Frequency | 4 kHz |
| Series | EvoSIGNAL Mini TwinLIGHT | Tone Type | Continuous/pulse |
| Bulb Type | LED | Touch to Acknowledge | No |
| Operator Size | 62mm | Number of Alarms | 2 |
| Operator Color | Yellow | Voltage Rating | 24 VAC/VDC |
| Light Color(s) | Yellow | Mounting | Modular |
| Light Function | Permanent or blinking (1 Hz ON for 470ms) | IP Rating | IP66 |
| Housing Material | Polycarbonate | Connection | Push-in terminal |
| Material | ABS/polycarbonate | Requires | Mounting adapter |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/46031075.pdf>
See store item page for other formats.