

46042074 Cut Sheet



WERMA EvoSIGNAL Mini TwinFLASH series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), clear/white, 62mm, 12 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46042074>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Mini TwinFLASH
Bulb Type	LED
Operator Size	62mm
Operator Color	Clear
Light Color(s)	Clear/white
Light Function	Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing)
Housing Material	Polycarbonate

Material	ABS/polycarbonate
Loudness Decibel	95 dB at 1m
Tone Frequency	4 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Number of Alarms	2
Voltage Rating	12 VAC/VDC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/46042074.pdf>
See store item page for other formats.