

# 46052060 Cut Sheet



WERMA EvoSIGNAL Mini TwinFLASH series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), blue, 62mm, 115-230 VAC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46052060>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Audible-visual signal beacon
<b>Series</b>	EvoSIGNAL Mini TwinFLASH
<b>Bulb Type</b>	LED
<b>Operator Size</b>	62mm
<b>Operator Color</b>	Blue
<b>Light Color(s)</b>	Blue
<b>Light Function</b>	Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing)
<b>Housing Material</b>	Polycarbonate
<b>Material</b>	ABS/polycarbonate
<b>Loudness Decibel</b>	95 dB at 1m
<b>Tone Frequency</b>	4 kHz
<b>Tone Type</b>	Continuous/pulse
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	115-230 VAC
<b>Mounting</b>	Modular
<b>IP Rating</b>	IP66
<b>Requires</b>	Mounting adapter

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>