

46122070 Cut Sheet



WERMA EvoSIGNAL Midi TwinFLASH series LED audible-visual signal beacon, 110 dB at 1m, (10) selectable tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), green, 85mm, 12/24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46122070>

Technical Specifications

| | |
|-----------------------------|--|
| Brand | WERMA |
| Item | Audible-visual signal beacon |
| Series | EvoSIGNAL Midi TwinFLASH |
| Bulb Type | LED |
| Operator Size | 85mm |
| Operator Color | Green |
| Light Color(s) | Green |
| Light Function | Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing) |
| Housing Material | Polycarbonate |
| Material | ABS/polycarbonate |
| Loudness Decibel | 110 dB at 1m |
| Tone Frequency | 3.3 kHz |
| Tone Type | (10) selectable |
| Touch to Acknowledge | No |
| Voltage Rating | 12/24 VAC/VDC |
| Mounting | Modular |
| IP Rating | IP66 |
| Requires | Mounting adapter |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |