

46131060 Cut Sheet



WERMA EvoSIGNAL Midi TwinLIGHT series LED audible-visual signal beacon, 110 dB at 1m, (10) selectable tone(s), permanent or blinking (1 Hz ON for 420ms), yellow, 85mm, 115-230 VAC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46131060>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Midi TwinLIGHT
Bulb Type	LED
Operator Size	85mm
Operator Color	Yellow
Light Color(s)	Yellow
Light Function	Permanent or blinking (1 Hz ON for 420ms)
Housing Material	Polycarbonate
Material	ABS/polycarbonate
Loudness Decibel	110 dB at 1m
Tone Frequency	3.3 kHz
Tone Type	(10) selectable
Touch to Acknowledge	No
Voltage Rating	115-230 VAC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document