

46131070 Cut Sheet



WERMA EvoSIGNAL Midi TwinLIGHT series LED audible-visual signal beacon, 110 dB at 1m, (10) selectable tone(s), permanent or blinking (1 Hz ON for 480ms), yellow, 85mm, 12/24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46131070>

Technical Specifications

Brand	WERMA	Loudness Decibel	110 dB at 1m
Item	Audible-visual signal beacon	Tone Frequency	3.3 kHz
Series	EvoSIGNAL Midi TwinLIGHT	Tone Type	(10) selectable
Bulb Type	LED	Touch to Acknowledge	No
Operator Size	85mm	Number of Alarms	10
Operator Color	Yellow	Voltage Rating	12/24 VAC/VDC
Light Color(s)	Yellow	Mounting	Modular
Light Function	Permanent or blinking (1 Hz ON for 480ms)	IP Rating	IP66
Housing Material	Polycarbonate	Connection	Push-in terminal
Material	ABS/polycarbonate	Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/46131070.pdf>
See store item page for other formats.