

46141070 Cut Sheet



WERMA EvoSIGNAL Midi TwinLIGHT series LED audible-visual signal beacon, 110 dB at 1m, (10) selectable tone(s), permanent or blinking (1 Hz ON for 480ms), clear/white, 85mm, 12/24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46141070>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Midi TwinLIGHT
Bulb Type	LED
Operator Size	85mm
Operator Color	Clear
Light Color(s)	Clear/white
Light Function	Permanent or blinking (1 Hz ON for 480ms)
Housing Material	Polycarbonate
Material	ABS/polycarbonate
Loudness Decibel	110 dB at 1m
Tone Frequency	3.3 kHz
Tone Type	(10) selectable
Touch to Acknowledge	No
Voltage Rating	12/24 VAC/VDC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document